



Optical properties	Mechanical properties	Colormetric properties																														
<b>Reflection factor</b>	<b>Reference thickness</b>	1 mm      2 mm      3 mm																														
$P_d = 0,911$	$d = 1,00 \text{ mm}$	<table border="1"> <tr> <td rowspan="5">Illuminant D65</td> <td>x</td> <td>0,284</td> <td>0,246</td> <td>0,220</td> </tr> <tr> <td>y</td> <td>0,493</td> <td>0,582</td> <td>0,637</td> </tr> <tr> <td>Y</td> <td>44,8</td> <td>25,2</td> <td>15,2</td> </tr> <tr> <td><math>\lambda_d</math></td> <td>541 nm</td> <td>535 nm</td> <td>532 nm</td> </tr> <tr> <td><math>P_e</math></td> <td>0,392</td> <td>0,561</td> <td>0,660</td> </tr> </table>	Illuminant D65	x	0,284	0,246	0,220	y	0,493	0,582	0,637	Y	44,8	25,2	15,2	$\lambda_d$	541 nm	535 nm	532 nm	$P_e$	0,392	0,561	0,660									
Illuminant D65	x			0,284	0,246	0,220																										
	y			0,493	0,582	0,637																										
	Y			44,8	25,2	15,2																										
	$\lambda_d$			541 nm	535 nm	532 nm																										
	$P_e$	0,392	0,561	0,660																												
<b>Spectral values guaranteed</b>	<b>Density</b>	<table border="1"> <tr> <td rowspan="5">Illuminant A</td> <td>x</td> <td>0,370</td> <td>0,306</td> <td>0,265</td> </tr> <tr> <td>y</td> <td>0,522</td> <td>0,596</td> <td>0,645</td> </tr> <tr> <td>Y</td> <td>39,7</td> <td>20,9</td> <td>12,1</td> </tr> <tr> <td><math>\lambda_d</math></td> <td>535 nm</td> <td>529 nm</td> <td>527 nm</td> </tr> <tr> <td><math>P_e</math></td> <td>0,307</td> <td>0,468</td> <td>0,576</td> </tr> </table>	Illuminant A	x	0,370	0,306	0,265	y	0,522	0,596	0,645	Y	39,7	20,9	12,1	$\lambda_d$	535 nm	529 nm	527 nm	$P_e$	0,307	0,468	0,576									
Illuminant A	x			0,370	0,306	0,265																										
	y			0,522	0,596	0,645																										
	Y			39,7	20,9	12,1																										
	$\lambda_d$			535 nm	529 nm	527 nm																										
	$P_e$	0,307	0,468	0,576																												
$\tau_i (450 \text{ nm}) \leq 0,21$	<b>Knoop hardness</b>	<table border="1"> <tr> <td colspan="5"><b>Notes</b></td> </tr> <tr> <td colspan="5">Ionically colored glass</td> </tr> <tr> <td colspan="5">Bandpass filter</td> </tr> <tr> <td colspan="5">DIN 58131</td> </tr> <tr> <td colspan="5"><b>Disclaimer</b></td> </tr> <tr> <td colspan="5">All data without tolerances are to be understood to be reference values.</td> </tr> </table>	<b>Notes</b>					Ionically colored glass					Bandpass filter					DIN 58131					<b>Disclaimer</b>					All data without tolerances are to be understood to be reference values.				
<b>Notes</b>																																
Ionically colored glass																																
Bandpass filter																																
DIN 58131																																
<b>Disclaimer</b>																																
All data without tolerances are to be understood to be reference values.																																
$\tau_i (514 \text{ nm}) \geq 0,67$	$\rho = 2,87 \text{ g/cm}^3$																															
$\tau_i (633 \text{ nm}) \leq 0,15$	<b>Thermal properties</b>																															
$\tau_i (725 \text{ nm}) \leq 0,07$	<b>Transformation temperature</b>																															
$\tau_i (1060 \text{ nm}) \leq 0,18$	$T_g = 451 \text{ }^\circ\text{C}$																															
	<b>Thermal expansion in <math>10^{-6}/\text{K}</math></b>																															
	$\alpha_{(-30^\circ\text{C}/+70^\circ\text{C})} = 9,2$																															
	$\alpha_{(20^\circ\text{C}/300^\circ\text{C})} = 10,6$																															
<b>Refractive indices</b>	<b>Chemical properties</b>																															
	<b>Chemical resistance</b>																															
	FR class = 0																															
$n_d (587,6 \text{ nm}) = 1,55$	SR class = 1																															
	AR class = 1																															
<b>Sellmeier coefficients</b>	<b>Resistance against humidity</b>																															
on request	Robust glass																															
	see pocket catalogue "Optical Filter Glass 2020", chapter 5.5																															
<b>Internal quality</b>																																
Bubble class 1																																



VG9



**Internal transmittance  $\tau_i$  at reference thickness**  
 The internal transmittance values, tabulated and graphically represented, are reference values only

$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$	$\lambda$ /nm	$\tau_i$
200	< 1,0E-05	500	6,130E-01	800	4,315E-02	1100	1,745E-01	2200	8,400E-01	3700	4,100E-01
210	< 1,0E-05	510	6,690E-01	810	4,327E-02	1110	1,824E-01	2250	8,472E-01	3750	4,175E-01
220	< 1,0E-05	520	6,980E-01	820	4,381E-02	1120	1,907E-01	2300	8,548E-01	3800	4,300E-01
230	< 1,0E-05	530	6,980E-01	830	4,462E-02	1130	2,013E-01	2350	8,614E-01	3850	4,420E-01
240	< 1,0E-05	540	6,690E-01	840	4,547E-02	1140	2,079E-01	2400	8,700E-01	3900	4,500E-01
250	< 1,0E-05	550	6,180E-01	850	4,674E-02	1150	2,184E-01	2450	8,736E-01	3950	4,542E-01
260	< 1,0E-05	560	5,520E-01	860	4,781E-02	1160	2,273E-01	2500	8,800E-01	4000	4,524E-01
270	< 1,0E-05	570	4,770E-01	870	4,890E-02	1170	2,372E-01	2550	8,800E-01	4050	4,429E-01
280	< 1,0E-05	580	4,010E-01	880	5,036E-02	1180	2,460E-01	2600	8,840E-01	4100	4,200E-01
290	< 1,0E-05	590	3,300E-01	890	5,300E-02	1190	2,562E-01	2650	8,830E-01	4150	4,015E-01
300	< 1,0E-05	600	2,650E-01	900	5,608E-02	1200	2,644E-01	2700	8,700E-01	4200	3,800E-01
310	< 1,0E-05	610	2,090E-01	910	5,926E-02	1250	3,044E-01	2750	6,870E-01	4250	3,543E-01
320	< 1,000E-05	620	1,640E-01	920	6,255E-02	1300	3,500E-01	2800	6,154E-01	4300	3,223E-01
330	< 1,000E-05	630	1,300E-01	930	6,600E-02	1350	4,000E-01	2850	6,050E-01	4350	2,884E-01
340	< 1,000E-05	640	1,070E-01	940	6,967E-02	1400	4,400E-01	2900	6,000E-01	4400	2,469E-01
350	< 1,000E-05	650	8,900E-02	950	7,392E-02	1450	4,901E-01	2950	5,890E-01	4450	2,054E-01
360	< 1,000E-05	660	7,500E-02	960	7,900E-02	1500	5,300E-01	3000	5,800E-01	4500	1,600E-01
370	< 1,000E-05	670	6,558E-02	970	8,434E-02	1550	5,702E-01	3050	5,626E-01	4550	1,140E-01
380	< 1,000E-05	680	5,811E-02	980	8,972E-02	1600	6,000E-01	3100	5,400E-01	4600	7,450E-02
390	< 1,000E-05	690	5,297E-02	990	9,538E-02	1650	6,371E-01	3150	5,183E-01	4650	5,248E-02
400	< 1,000E-05	700	4,985E-02	1000	1,020E-01	1700	6,700E-01	3200	5,000E-01	4700	3,251E-02
410	7,621E-04	710	4,816E-02	1010	1,091E-01	1750	6,955E-01	3250	4,787E-01	4750	2,203E-02
420	5,715E-03	720	4,695E-02	1020	1,162E-01	1800	7,200E-01	3300	4,600E-01	4800	1,614E-02
430	1,963E-02	730	4,597E-02	1030	1,230E-01	1850	7,407E-01	3350	4,392E-01	4850	1,230E-02
440	5,343E-02	740	4,533E-02	1040	1,295E-01	1900	7,600E-01	3400	4,213E-01	4900	1,000E-02
450	1,170E-01	750	4,479E-02	1050	1,360E-01	1950	7,775E-01	3450	4,118E-01	4950	7,534E-03
460	2,160E-01	760	4,422E-02	1060	1,430E-01	2000	7,900E-01	3500	4,034E-01	5000	5,000E-03
470	3,250E-01	770	4,387E-02	1070	1,510E-01	2050	8,086E-01	3550	4,000E-01	5050	2,773E-03
480	4,290E-01	780	4,354E-02	1080	1,590E-01	2100	8,200E-01	3600	4,000E-01	5100	1,455E-03
490	5,300E-01	790	4,328E-02	1090	1,670E-01	2150	8,312E-01	3650	4,024E-01	5150	6,637E-04