



FOCAL LENGTH (EFL): 400 ± 4
 BACK FOCAL LENGTH (BFL): 396,7

1 1550nm V-COAT
 R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 206,72 CX Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING			TITLE	40mm Dia x 400mm FL, 1550nm V-Coat Coated, Plano-Convex Lens
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO
			SHEET SIZE	A4
			SHEET	1 OF 1